MT2 RAPID

Optionals



OZONE



HACCP USB



WATER COOLED CONDENSER



VERTICAL CONTROL PANEL



ADDITIONAL INSTALLATION KIT



SOUNDPROOF CONDENSING UNIT



400 mm TUNNEL LENGTH EXTENSION





Capacity



400 kg

+90°C → +3°C



370 kg

+90°C → -18°C

Trolleys 800 x 850 mm

Trolleys 450 x 650 GN

Features

Code number	MT2	MT2+1/2
Power supply	400V/3N/50HZ	400V/3N/50HZ
Outside length	2230 / 980 mm	2230 / 980 mm
Depth	1830 / 1630 mm	2230 / 2030 mm
Height	2630 / 2080 mm	2630 / 2080 mm
Capacity 800x850 mm / 450x650 GN	2/4	2/6
Output chilling (+90°C/+3°C)	400 kg	400 kg
Output freezing (+90°C/-18°C)	370 kg	370 kg
Electronic card	BASE	BASE
Absorbed power	17.2 kW	17.2 kW

REMOTE UNIT FEATURES (MAX DISTANCE 15 M)


Power supply	400V/3N/50HZ	400V/3N/50HZ	
Refrigeration Power (Cond:-20°/+40 (°C)	33.7 kW -22 HP	33.7 kW -22 HP	
Absorbed power (Cond:-20°/+40 (°C)	16.2 kW	16.2 kW	
Diameter Discharge Pipe (<15 mt)	22 mm	22 mm	
Diameter Suction Pipe (<15 mt)	42 mm	42 mm	
Diameter Hot Gas Pipe (<15 mt)	22 mm	22 mm	
Gas	R 452a (GWP2141)	R 452a (GWP2141)	
Dimensions	2200 x 1300 x 1850 mm	2200 x 1300 x 1850 mm	







MT2 RAPID




For running 24 hours a day





Excavation example












MT2 RAPID


Alternative solutions Control Panel Position



Horizontal control panel











REMOTE UNIT FEATURES

Machine delivered without condensing unit - Disclaimer Clause

Castelmac guarantees only the good functioning of the components of the machine. It's excluded from the warranty:


- the cooling performance of the machine
- · malfunctioning or damages due to the partial on not complete connection of the machine with the central cooling unit or the not original condensing unit. In particular there is no warranty on damages on the machine due to the missed connection of the alarm input which stops the machine in case of alarm coming from the central cooling unit or the not original condensing unit. Hot gas defrosting available only if hot gas supplied (distance < 25 m). Alternative air defrosting available from control panel.

CONNECTION TO CENTRAL COOLING UNIT

- Blast Freezing function must be disabled (do not work)
- Use the freezing line (-28°C / 30°C Evaporation)
- Output signal supplied for liquid line valve control (valve not supplied)
- · Input signal available for general alarm from the central cooling unit, which stops the machine

CONNECTION TO CONDENSING UNIT NOT SUPPLY BY TECNOMAC

- · Output signal supplied for switch on compressor
- Output signal supplied for switch on hot gas valve (if present)
- · Input signal available for alarm coming from the condensing unit, which stops the machine



CONDENSING UNIT WITH BOX





